



Part Number : 1301370232

Series Number : 130137

Product Category : Power Distribution

Product Description : Watertite GFCI Multiple Outlet FD Box with Ground Continuity Monitor, (1) L5-15 Duplex with Flip Lids, 1.83m (6.0') Cord Length, 14/3 SOOW Cord, NEMA L5-15 Watertite Plug

Status : Active

Engineering Number : 3302GGFL143

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Relevant

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power Distribution
Series	130137

Description	Watertite GFCI Multiple Outlet FD Box with Ground Continuity Monitor, (1) L5-15 Duplex with Flip Lids, 1.83m (6.0') Cord Length, 14/3 SOOW Cord, NEMA L5-15 Watertite Plug
Enclosure Rating	NEMA 4X
NEMA Configuration	NEMA L5-15
Product Name	Watertite
Type	GFCI Multiple Outlet Box
UPC	78678898116

## Electrical

Current - Maximum per Contact	15.0A
GFCI	Yes
GFCI Reset	Manual
Ground Continuity Monitor	Yes
Open Neutral Relay	No
Voltage - Maximum	120V

## Physical

Cord Diameter	13.59mm (.535")
Cord Grip Body Size	F3 3/4"
Cord Length	1.83m (6.0')
Cord Type	14/3 SOOW
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Nylon
Mounting Style	Portable
Number of Receptacles	1
Packaging Type	Carton
Receptacle Type	Duplex

---

This document was generated on Mar 22, 2025