




[+ HARNESSING](#)
[CABLE BRAIDS](#)



✓ Active

TE CONNECTIVITY (TE)
RAY-101-20.0(10)

RAY-101-20.0(10)
TE Internal Number: CQ50363001

[EU RoHS Compliant](#)
[EU ELV Compliant](#)

Product Type Braid
Plating Tin
Braid Material Copper
Braid Coverage (%) 93

[↓ PRODUCT DRAWING](#)
English

DOCUMENTATION

Product Drawings

Customer Drawing
PDF
English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type Braid

Electrical Characteristics

DC Resistance (Nominal) (mΩ) 2.32

Body Features

Plating Tin
Braid Material Copper

Dimensions

Length (ft) 32.8
Length (m) 10
Weight (Nominal) (kg/km) 95

Usage Conditions

Operating Temperature Range (°C) -65 – 150

Packaging Features

Packaging Quantity 10
Packaging Method Bag

Other

Braid Coverage (%) 93

Statement of Compliance

Statement of Compliance
PDF