

[→ Honeywell.com](#) [→ Automation & Control Solutions](#)[HOME](#)[ABOUT US](#)[KEY INDUSTRIES SERVED](#)[PRODUCTS & INFORMATION](#)[NEWS & EVENTS](#)[SALES & SUPPORT](#)[LOGIN](#)

## Honeywell Sensing and Control

Search



### narrow your search

#### Products

- Controls Monitoring and Lighting (352)
- Machine Safety (1727)
- Sensors (5910)
- Switches (9781)
- Wireless (45)

#### Technology

- Capacitive (26)
- Control and Instrumentation (1054)
- Electromechanical (9307)
- Microstructure (1495)
- Thick Film (1409)
- More...

### new products

#### New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site  
WGLA and WPMW  
XYR6000™

[find out more](#)

### white papers

Wireless Switches Offer  
Unlimited Benefit

Basic Switches Are Not Created  
Equal

Applying Precision Switches  
Sensors for Medical Devices

New Ways to Measure Torque

Choosing Safety Switches

Specifying Hour Meters

### Need help?

[Click here to contact us](#)

### LSA1A4

( Home : Products : Switches » MICRO SWITCH™ Limit Switches » MICRO SWITCH™ Heavy-Duty Limit Switches » HDLS )



Actual product appearance  
may vary.  
[click here to download Hi-Res image](#)

Series HDLS Plug-in: Side Rotary; 1NC 1NO SPDT Snap Action;  
0.5 in - 14NPT conduit

[Sales & Service](#)[Distributor Inventory](#)[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

#### Product Specifications

Availability	Global
Operating Force (OF)	0.45 N m [4 in lb] max.
Pretravel (PT)	15° max.
Overtravel (OT)	60° min.
Differential Travel (DT)	5° max.
Product Type	MICRO SWITCH™ Heavy-Duty Limit Switches
Actuator	Side Rotary
Lever Type	Lever Not Included - Reference Lever Required Accessory
Circuitry	1NC 1NO SPDT Snap Action, Double Break
Ampere Rating	10 A (Thermal)
Supply Voltage	600 Vac and 250 Vdc max.
Housing Material	Zinc Die-Cast
Termination Type	0.5 in - 14NPT Conduit
Housing Type	HDLS Plug-in
Series Name	HDLS
Sealing	NEMA 1, 3, 4, 4X, 6, 6P, 12, 13
UL File #	E37138
Operating Temperature	-12 °C to 121 °C [10 °F to 250 °F]
Comment	Head assembled with shaft to the left of switch front
Agency Approvals and Standards	UL, CE, CSA, CCC. EN60947-1, EN60947-5-1
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Sealed	Industrial

### contacts

Customer Service  
Technical Support  
Global Sales & Service  
View Site Demo  
Site Comments?

### meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

### my links

Login to iCOM  
Login to Rep/AD Portal  
Login to Digital University

### News Center

HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION

HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO

HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION

HONEYWELL INTRODUCES MICROPOWER OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT

**MICRO SWITCH  
Anniversary site**

[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)