TM1000 Series




Applications / Markets


Portable Equipment


Gaming and Computer


Security Devices


Medical

RoHS

Specifications

Electrical Rating: 20mA, 20V (AC or DC)
Life Expectancy: 1,000,000 Cycles
Contact Resistance: 5Ω Max.
Insulation Resistance: 100MΩ Min. at 500VDC
Dielectric Strength: 500VAC for 1 Minute
Operating Temperature: -25°C to 70°C

Function: SPST

Features & Benefits


- **1,000,000 cycle life expectancy**
- **The switch is triggered when tilted 45 degrees of the horizontal**
- **Environmentally friendly, contains no mercury**


Part Number Configurator

Series	Model	Contact Material
TM	1000	Q - Silver


Specifications subject to change without notice

Downloaded from Arrow.com.






PCB LAYOUT




SCHEMATIC

ON - OFF ANGLES



BODY DIMENSIONS



Downloaded from Arrow.com.