



Honeywell Scanning & Mobility



### Voyager 1200g

Built on the platform of the world's best-selling single-line laser scanner, Honeywell's Voyager® 1200g delivers aggressive scan performance on virtually all linear bar codes, including poor quality and damaged codes. Updated object detection, and automatic in-stand detection and configuration enable class-leading presentation scanning that maximizes throughput. Superior scan performance matched with a reliable design combine to provide a versatile linear scanning solution.

[Zoom](#)

Features & Benefits

Accessories

Documents

Images

Software

Links

#### Voyager 1200g Accessories

**Power**  
46-00525 STD Power Supply: NA plug, 1.0A @ 5.2VDC, 90-255VAC @

**Cables**  
CBL-500-300-C00 STK Cable: USB, black, Type A, 3m (9.8'), coiled, 5V host power  
CBL-500-300-S00 STK Cable: USB, black, Type A, 3m (9.8'), straight, 5V host power  
CBL-020-300-C00 Cable: RS232 (5V signals), black, DB9 Female, 3m (9.8'), coiled, 5V external power with option for host power on pin 9 STD  
CBL-120-300-C00 Cable: RS232C (+/-12V signals), black, DB9 Female, 3m (9.8'), coiled, 5V external power with option for host power on pin 9 STD  
CBL-220-300-C00 Cable: RS232 (+5V signals); black, DB9 Male; 3m (9.8'), coiled, external power with option for host power on pin 9 STD  
CBL-420-300-C00 Cable: RS232 Aux, black, 3m (9.8'), coiled, for connection to Honeywell Stratos scanners STD  
CBL-500-500-C00 STD Cable: USB, black, Type A, 5m (16.4'), coiled, 5V host power  
CBL-503-300-C00 STD Cable: USB, black, 12V locking, 3m (9.8'), coiled, 5V host power  
CBL-600-400-C00 STD Cable: IBM 46xx Port 9b, 12V Power, coiled, 4m (13.1')  
CBL-720-300-C00 Cable: Keyboard Wedge (KBW), black, PS2, 3m (9.8'), coiled, 5 V external power with option for host power STD

**Stands/Holders**  
STND-19R02-002-4 Stand: gray, 19cm (7.5") stand height, rigid Voyager-like plastic pole, weighted tripod base, Voyager 1200 cup STK  
HOLDER-004-U STD Holder: desktop/wall mount  
HOLDER-005-W STD Holder: wall mount hook  
STND-23F02-002-4 Stand: gray, 23cm (9") stand height, flexible rod, weighted tripod base, Voyager 1200 cup STD  
STND-23F03-002-4 Stand: gray, 23cm (9") stand height, flexible rod, weighted mid-sized universal base, Voyager 1200 cup STD