

Home / Without Touch / P1210XGF1MB00

P1210XGF1MB00

Dimensions	9,5 × 260,5 × 203 mm
Panel Size (inch)	12.1"
Format	4:3
Display Resolution	XGA
Pixel Resolution	1024 x 768
Orientation	Landscape
Panel Type	SFT
Viewing Angle	88, 88, 88, 88
Surface	AG
Interface	LVDS
Interface Detail	LVDS
Luminance (cd/m²)	500
Color Gamut	72%
Contrast	1000:1
Response Time (ms)	25
Backlight Driver	integrated
Backlight Lifetime (khrs)	50
Operating Temperature (°C)	-30~80
Storage Temperature (°C)	-40~90
Comment	SFT