HellermannTyton

# Technical data sheet

## Article number:
## 561-00699 WIC0-9




| | |
|---|---|
| **Product Group** | Pre-printed cable markers |
| **Product Family** | WIC, snap on |
| **Material** | Polyamide 6.6 (PA66) |
| **Colour** | White (WH) |

| | |
|---|---|
| **Application Tool** | WIC Tool |
| **Bundle Ø max.** | 2.20 mm |
| **Bundle Ø min.** | 0.80 mm |
| **Flammability** | UL 94 V0 |
| **Height (H)** | 5.50 mm |
| **Length (L)** | 3.00 mm |
| **Marking Text** | 9 |
| **Operating Temperature** | -40 °C to +85 °C |
| **Package Content** | 1000 pcs. |
| **Package Content packed in** | box |
| **Print Method** | inkjet print |
| **Specifications** | EN 60062, IEC 304 |
| **Width (W)** | 5.00 mm |
| **Wire Size Range (mm²)** | 0.15-0.75 mm² |

HF RoHS

created on 22. May 2026, 6:31 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.