



Part Number : [1301030057](#)

Product Description : Watertite Wet Location Incandescent Hand Lamp, 100W with Cast Aluminum Guard, Cord Type 16/3 SOOW, 15.24m (50.0') Cord Length

Series Number : 130103

Status : Active

Product Category : Lamps and Lights

Engineering Number : 1207B163



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130103
Description	Watertite Wet Location Incandescent Hand Lamp, 100W with Cast Aluminum Guard, Cord Type 16/3 SOOW, 15.24m (50.0') Cord Length
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Name	Watertite
Type	Hand Lamps
UPC	78678861363

Agency

CSA	LR85374
-----	---------

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120V AC

Physical

Bulb Type	Incandescent
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	120.65mm (4.750")
Duty	Wet Location
Guard Included	Yes
Guard Type	Screw Release
Height	457.20mm (18.000")
Lamp Type	A21

Length	N/A
Material - Globe	Tempered Glass
Material - Guard	Cast Aluminum
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton

This document was generated on Sep 10, 2025