95-22001

ACTIVE

EMI Connector Gasket, Nickel Plated Graphite (Ni/C) Filler, .8 mm [.031 in] Thick, 35.8 mm [1.409 in] Width, Kemtron 95 Series

View all D-Sub Conn Gaskets for RFI/EMI Shielding (40)





Kemtron | Kemtron 95 Series

TE Internal #: **2430137-1**
TE Internal Description: **Conn G SNG 0.8mm D-Sub 9 Pin**

Gasket Type : **EMI Connector Gasket**
Filler Material : **Nickel Plated Graphite (Ni/C)**
Product Thickness : **.8 mm [.031 in]**
Product Width : **35.8 mm [1.409 in]**
Operating Temperature Range : **-55 – 160 °C [-67 – 320 °F]**

Documents | Features | Product Compliance

Product Drawings

95-ELASTOMER-D-SUB-RANGE
ENG_CD_95-D-CONNECTOR-GASKETS_A1.Pdf
English

CAD Files

3D PDF
3D_CVM_CVM_2430137-1_A.pdf
3D

Customer View Model
ENG_CVM_CVM_2430137-1_A.3d_igs.zip
English
ENG_CVM_CVM_2430137-1_A.3d_stp.zip
English
ENG_CVM_CVM_2430137-1_A.2d_dxf.zip
English

Datasheets & Catalog Pages

performance-materials-brochure
ENG_CS_performance-materials-brochure_1.pdf
English

Connector Gaskets for RFI/EMI Shielding
ENG_DS_connector-gasket_G.pdf
English

Product Specifications

Application Specification
ENG_SS_114-120007_A3.pdf
English

Product Specification
ENG_SS_108-120068_C.pdf
English

Product Change Notification

View Product Change Notification

Terms of Use | Privacy | US Privacy | Cookie Policy | Accessibility | Security | Site Map © 2026 TE Connectivity. All Rights Reserved.

Downloaded from Arrow.com.