

Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- Accessory
- M5
- Guided M8
- M8
- M10.5
- M12 (A)
- M12 (B)
- M12 (D)**
- M12 (I)
- M12 (K)
- M12 (L)
- M12 (S)
- M12 (T)
- M12 (X)
- M23
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



M12D-04PMMR-SF7003

Operating Temperature: -40°C ~ +105°C
 Transmission Speed: N/A
 Shielded: Metal, Non-shielded
 Jacket Material: N/A
 Certificate: UL1977, UL2238, UL1863

You must login first for view the price

Quantity

[Add to Cart](#) [Inquiry](#) [Heart](#)

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type [Search](#)

M Series, CAP-WBDMQPC1 -20°C ~ +80°C	M Series, CAP-WBDMQPC1 -40°C ~ +105°C	M Series, CAP-WBDMQPC1 -40°C ~ +105°C	M Series, M12, D... M12D-04BFFA... -40°C ~ +105°C	M Series, M12, D... M12D-04BFFA... -40°C ~ +105°C	M Series, M12, D... M12D-04BFFB... -40°C ~ +105°C
<input type="text" value="0"/>	<input type="text" value="0"/>	<input type="text" value="0"/>	<input type="text" value="0"/>	<input type="text" value="0"/>	<input type="text" value="0"/>

[Add to Cart](#) [Inquiry](#)

Specifications	Download / CAD
Nominal Current 4A	Connector Type Receptacle
Shielded Metal, Non-shielded	No. of Contacts 04
Connector Gender Male	Backshell Hexagonal
Mating Style Screw Thread	IP Rating IP67
Assembly Style PCB 90°	

[More Options](#)

People Also Bought

- M12D-04PMMR-...
- CB-04AFFM-RL7A10
- AB-CB05ML-CBBR-...
- AB-CD12FL-CDFR-...
- AB-BD04FR-BDBL-...