



Part Number : [936011629](#)

Product Description : Heavy-Duty Standard (STD)
Double Lever Hood, Die-cast Aluminum, with 4 Pegs,
Top Entry, Size 10B «57x27», M40 Thread, High
Construction, Grey

Series Number : 93601

Status : Active

Product Category : Heavy-Duty Connectors

Engineering Number : 7810.6444.5

Documents & Resources

Drawings

[936011629_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per ED/71/2019 (16 July 2019)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Standard (STD) Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Top Entry, Size 10B «57x27», M40 Thread, High Construction, Grey
Component Type	Double Lever Hood
IP Rating	IP66
Product Name	Heavy-Duty Connectors
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191838342

Agency

CSA	256883
UL	E249674

Electrical

Voltage - Maximum	500V
-------------------	------

Physical

Component Size	10B «57X27»
Entry Location	Top
Hood Coating	Polyester Powder

Hood Color	GREY RAL 7037
Lock to Mating Part	Yes
Material - Hood	Die-cast Aluminum
Material - Peg	Stainless Steel
Net Weight	184.000/g
Number of Pegs	4
Packaging Type	Bag
Thread Size	M40
Thread Type	(M) Metric

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Size 10B «57x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts

This document was generated on Sep 23, 2025