








Amphenol
FCi
© 2016 AFCI



- NOTE:
- MATERIAL:
HOUSING: NYLON 66, HALOGEN FREE
UL94V-0, COLOR: OPTIONS
 - REFER GS-20-0399 APPLICATION SPECIFICATION FOR MATING CONNECTOR.
 - PRODUCT SPECIFICATION: GS-12-1291.
 - PACKAGE SPECIFICATION: GS-14-2419 (BULK PACKED)
 - APPLICATION SPECIFICATION: GS-20-0399.
 - LEAD FREE PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-47-0004
 - PART NUMBER SCHEME:
10132445- XX X LF
POS. CODE: ——— LEAD FREE
02: 2 POS. ——— COLOR,
04: 4 POS. ——— BLANK: BLACK
24: 24 POS.

DIMENSIONAL & PART NO. TABLE:

PART NO.	POS	A	B
10132445-02XLF	2	3.85	3.85
10132445-04XLF	4	3.0	6.85
10132445-06XLF	6	6.0	9.85
10132445-08XLF	8	9.0	12.85
10132445-10XLF	10	12.0	15.85
10132445-12XLF	12	15.0	18.85
10132445-14XLF	14	18.0	21.85
10132445-16XLF	16	21.0	24.85
10132445-18XLF	18	24.0	27.85
10132445-20XLF	20	27.0	30.85
10132445-22XLF	22	30.0	33.85
10132445-24XLF	24	33.0	36.85

mat'l. code				surface ISO 1302		tolerance ISO 406 ISO 1101		projection 		product family MINITEK PWR3.0 HCC													
ltr	ecn no		dr	date		tolerances unless otherwise specified						title MINITEK PWR3.0 REC. HSG D/R HIGH CURRENT											
A			TAI	2015-02-25		angles linear		.0±.50															
B	ELX-N-28240		TONY	2017-10-24				.00±.30															
C	ELX-I-43460		ASLAM	2022-01-21				.000±.20															
D	ELX-I-50412		VISHNU	2024-01-22		0°±3°		scale N.T.S.						dwg no sheet 1 of 2 size A3									
						dr		KENNY TAI		2015-02-03													
						engr		VISHNU		2024-01-22													
						chr		MITHUN PAUL		2024-01-22													
						appd		SPK		2024-01-22													
sheet index		revision sheet		D	D																		

