



Part Number : 1300950229

Product Description : Heavy Duty Wire Mesh Slack Grip Cable, Closed Mesh, Double Weave, Offset Eye, Medium Mesh Length 0.432m (17.00"), Approximate Break Strength 2494.76kg (5500 lbs)

Series Number : 130095

Status : Active

Product Category : Cable Grips

Engineering Number : 36103

Documents & Resources

Drawings

Drawing 1300950229_sd.pdf

Product Environment Compliance

Compliance

| | |
|--------------------|--------------|
| China RoHS | Not Reviewed |
| EU ELV | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC | Not Reviewed |
| EU RoHS | Not Reviewed |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

| | |
|--------|--------|
| Status | Active |
|--------|--------|

| | |
|----------------|---|
| Category | Cable Grips |
| Series | 130095 |
| Description | Heavy Duty Wire Mesh Slack Grip Cable, Closed Mesh, Double Weave, Offset Eye, Medium Mesh Length 0.432m (17.00"), Approximate Break Strength 2494.76kg (5500 lbs) |
| Product Family | Support Grips |
| Product Name | Heavy Duty |
| Type | Pulling Grip |
| UPC | 78678836103 |

Agency

| | |
|-----|---------|
| CSA | LR32159 |
|-----|---------|

Physical

| | |
|----------------------------|------------------------------|
| Approximate Break Strength | 2494.76kg (5500 lbs) |
| Bale Length | N/A |
| Body Style | Straight |
| Cable Diameter | 31.75-37.85mm (1.250-1.490") |
| Color - Grommet | N/A |
| Eye Type | Offset |
| Gender | N/A |
| Material - Body | N/A |
| Material - Grip | Galvanized Steel |
| Mesh Length | 0.432m (17.00") |
| Number of Holes | N/A |
| O-Ring | N/A |
| Thread Size | N/A |

This document was generated on Jul 10, 2024