



Part Number : [1300611031](#)


Product Description : BradPower A-Size (7/8"-M22)
Single-Ended Cordset, 3 Poles, Female (Straight) to
Pigtail, 14 AWG, Black TPE Cable, 10.0m (32.81') Length

Series Number : 130061

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 103000K20M100E



Documents and Resources

Drawings

[1300611031_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead; diphenyl(2,4,6-trimethylbenzoyl)phosphine oxide per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130061
Description	BradPower A-Size (7/8"-M22) Single-Ended Cordset, 3 Poles, Female (Straight) to Pigtail, 14 AWG, Black TPE Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Name	BradPower A-Size
Protocol	FF
Type	Single Ended
UPC	78172550807

Agency

UL	E258922
----	---------

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	600V

Physical

Cable Diameter	8.63mm (.340")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Connector End A	BradPower A-Size (7/8"-M22)

Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	114.000/g
Orientation	Straight to Pigtail
Poles	3
Temperature Range - Operating	-20° to +90°C
Wire/Cable Type	TC-ER
Wire Size (AWG)	14

This document was generated on Dec 16, 2025