Part Number : 190030103
Product Description : InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm^2), Continuous Molded Strip, Tab 4.75 x 0.51mm, Yellow
Series Number : 19003
Status : Active
Product Category : Quick Disconnects
Engineering Part Number : M-2210C



Documents and Resources

Drawings

190030103_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-008-001.pdf

PS-19902-011-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Melamine per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19003
Description	InsulKrimp Quick Disconnect, Female, for 24-26 (0.20-0.12mm^2), Continuous Molded Strip, Tab 4.75 x 0.51mm, Yellow
Comments	Funnel Entry
Product Name	InsulKrimp
Type	Standard Quick Disconnect
UPC	800753128903

Electrical

Voltage - Maximum	600V

Physical

Barrel Type	Closed
Color - Resin	Yellow
Gender	Female
Glow-Wire Capable	No
Insulated	Fully
Insulation	Nylon (PA)
Lock to Mating Part	No
Material - Metal	Brass

Downloaded from Arrow.com.

Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	0.714/g
Orientation	Straight
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	No
Tab Thickness	0.51mm
Tab Width	4.75mm
Temperature Range - Operating	-65° to +105°C
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.90mm max.
Wire Size (AWG)	24, 26

Solder Process Data

Lead-Free Process Capability	N/A

Application Tooling

Global

Description	Part Number
Mini-Mac Applicator	638830600

Downloaded from Arrow.com.