


TABLE 1

CLASS	MATERIAL/FINISH
F	ALUMINIUM/NICKEL PLATED
K	STAINLESS STEEL/PASSIVATED
W	ALUMINIUM/OLIVE DRAB CADMIUM PLATED
Z	ALUMINIUM/ZINK NICKEL PLATED

TABLE 2

SHELL SIZE	A MAX	B MAX	C THREAD	D MIN	E MAX	G MAX	H MAX	J MAX	I MIN	N	MAXIMUM ENTRY SIZE
09	21,79	15,24	M12x1,0-6H	6,70	16,76	14,85	10,20	31,05	2,90	12	D
11	24,99	18,21	M15x1,0-6H	9,90	16,76	16,60	13,70	34,21	2,90	16	F
13	29,39	21,18	M18x1,0-6H	12,80	16,76	18,15	16,80	37,95	2,90	20	H
15	32,49	25,14	M22x1,0-6H	16,00	16,76	19,50	17,90	39,65	2,90	24	J
17	35,71	28,12	M25x1,0-6H	19,20	16,76	21,10	21,20	41,25	2,90	28	K
19	38,50	31,09	M28x1,0-6H	21,40	16,76	22,10	23,20	43,75	2,90	32	K
21	41,70	34,04	M31x1,0-6H	24,60	16,76	23,60	26,20	46,91	2,90	36	L
23	44,91	36,90	M34x1,0-6H	27,70	16,76	25,20	29,40	50,10	2,90	40	M
25	47,98	39,88	M37x1,0-6H	30,90	16,76	26,90	32,60	53,26	1,70	44	M

TABLE 4

CABLE ENTRY SIZE CODE	AA +/-0,1	BB +/-0,1	CC +/-0,3	DD +0,2/-0
A	4,7	7,7	12,2	1,12
B	6,4	9,4	14,0	1,12
C	7,9	11,0	15,5	1,12
D	9,5	12,6	17,1	1,12
E	11,1	14,1	18,7	1,12
F	12,7	15,7	20,3	1,12
G	15,9	18,9	23,5	1,12
H	19,1	22,0	26,7	1,12
J	22,2	25,2	29,8	1,75
K	25,5	28,4	33,0	1,75
L	28,6	31,5	36,2	1,75
M	31,8	34,7	39,4	1,75

EN3660-062W15B

- SERIES
- CLASS, MATERIAL FINISH (TABLE 1)
- SHELL SIZE (TABLE 2)
- CABLE ENTRY SIZE CODE (TABLE 4)

* NOTES:

1 - MINIMUM PENETRATION OF ØD FROM FRONT OF SERRATIONS
2 - PLEASE NOTE THERE MAY BE CROSSOVER DEPENDENT ON DIAMETER AND PITCH

DRAWN	W.RUST	DATE 26/04/2018
SALES APPR	H.TAILLANDIER	26/04/2018
DESIGN APPR	M.PAUL	17/12/2014
PROD APPR	J.STEPHENSON	17/12/2014
QUAL APPR	P.REES	17/12/2014
ISSUE 4	CRN 26875	
NCAGE CODE U5792	WEIGHT	

3RD ANGLE PROJECTION
NOT TO SCALE

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS IN MILLIMETRES
GENERAL TOL
LINEAR +/-0,25MM
ANGULAR +/- 3°

MATERIAL
SEE ABOVE
FINISH
SEE ABOVE

POLAMCO LTD
www.polamco.com
WESTON LOCK
LOWER BRISTOL ROAD
BATH BA2 1EP

ASSY USED ON: MIL-DTL-38999 SERIES III & IV

TITLE: 90° ANTI-DECOUPLING BANDING ADAPTOR

PART NUMBER: EN3660-062*****

DRAWING NO: P18068

SHT 1

THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.

Downloaded from Arrow.com.