



Part Number : [1300940491](#)
Product Description : Bus-Drop Support Grip,
Single "U" Eye, Cable Diameter 7.62-10.92mm
(.300-.430"), Approximate Break Strength 498.95kg
(1100 lbs)
Series Number : 130094
Status : Active
Product Category : Cable Grips
Engineering Number : 36562



Documents & Resources

Drawings

[1300940491_sd.pdf](#)
[PK-130227-004-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Bus-Drop Support Grip, Single "U" Eye, Cable Diameter 7.62-10.92mm (.300-.430"), Approximate Break Strength 498.95kg (1100 lbs)
Product Name	Bus-Drop
Type	Support Grip
UPC	78678836562

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	498.95kg (1100 lbs)
Bale Length	0.229m (9.00")
Body Style	Straight
Cable Diameter	7.62-10.92mm (.300-.430")
Color - Grommet	N/A
Eye Type	Single
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.114m (4.50")
Net Weight	41.508/g
Number of Holes	N/A

O-Ring	N/A
Thread Size	N/A

This document was generated on Sep 18, 2025