




TERMINATION:	
P1	COLOR
1	BLACK
2	RED
3	GREEN
4	YELLOW

Extended Length ("L2")	Typical Retracted Length ("L1")
60.0 Inches - 69.0 Inches	13.0 Inches
1,524.0MM-1,752.6MM	330.2MM

Material:

- Plug Housing: Polycarbonate, clear
- Plug Terminal: 0.36"[0.14MM] Thick Phosphor Bronze
- Connector: 50μ" of Selective Gold Contact Plating
 - Area, Gold flash over the remainder
 - Over 2.54μm[.000100] thick nickel underplate
- Conductor(X4C): 26AWG (0.12X12) Bare Copper
- Insulation(X4C): PP6331 ID 0.95-1.0
- Jacke: PVC No UL 80 P
- Package: Individual PE Bag

[illegible]

Item No.	AT-C-26-4/4/S-5-OE		
Title	NON-UL 26 AWG (0.12X12)*4C, O.D.: 2.4*4.8MM, Reverse Plug, 50μ" of contact plating, SILVER		
Drawing No.	rev00		
Replace	Sheet		

