

Plastic label - UC-EMLP (60X30) YE - 0822657

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Plastic label, Sheet, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: adhesive, lettering field size: 60 x 30 mm, Number of individual labels: 3

Your advantages

- ✓ The UC-EMLP ... UniCard marking range includes self-adhesive device markers with good adhesive properties
- ✓ The wide temperature range means that the labels can be used in control cabinets as well as the field
- ✓ The sheets provide space for including function texts
- ✓ The markers, which are supplied in uniform sheets, can be printed onto quickly and easily using the BLUEMARK LED
- ✓ The format automatically ensures printing with a high degree of positioning accuracy



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 046356 328616 |
| GTIN | 4046356328616 |
| Weight per Piece (excluding packing) | 14.000 g |
| Custom tariff number | 39269097 |
| Country of origin | Poland |

Technical data

Dimensions

| | |
|------------|-------|
| Length (b) | 30 mm |
| Width (a) | 60 mm |

Ambient conditions

Plastic label - UC-EMLP (60X30) YE - 0822657

Technical data

Ambient conditions

| | |
|---------------------------------|---|
| Ambient temperature (operation) | -40 °C ... 120 °C |
| Recommended storage conditions | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |

General

| | |
|--|--|
| Color | yellow |
| Components | free from silicone and halogen |
| Material | PA |
| Flammability rating according to UL 94 | V2 |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 3 |
| Number of individual labels per row | 1 |
| Mounting type | adhesive |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 2 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 2 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 2 |
| Testing substances harmful to the wetting properties of lacquers (LABS conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |
| UV resistance | Following ISO 4892-2:2013-03 |
| Result | Test passed |
| Test duration | 96 h |
| Test for wipe resistance of inscriptions | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Testing in a condensation changing climate in the presence of sulfur dioxide | DIN 50018:2013-05 |
| Result | Test passed |
| Climate level | AHT 1,0 S |
| Cycles | 2 |
| Salt spray test | DIN EN 60068-2-11:2000-02 |
| Result | Test passed |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27400629 |
| eCl@ss 11.0 | 27281103 |
| eCl@ss 4.0 | 24190200 |
| eCl@ss 4.1 | 24190200 |

Plastic label - UC-EMLP (60X30) YE - 0822657

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 5.0 | 27149100 |
| eCl@ss 5.1 | 27141100 |
| eCl@ss 6.0 | 27149100 |
| eCl@ss 7.0 | 27149129 |
| eCl@ss 9.0 | 27400629 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 6.0 | EC001288 |
| ETIM 7.0 | EC001288 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39131504 |
| UNSPSC 18.0 | 39131504 |
| UNSPSC 19.0 | 39131504 |
| UNSPSC 20.0 | 39131504 |
| UNSPSC 21.0 | 39131504 |

Accessories

Accessories

Magazine

Magazine - P1 UC-MAG 6 - 5146121



Magazine, for CMS-P1-PLOTTER and PLOTMARK, for accommodating UC-EMP..., UC-EMLP...

Printing system accessories

Plastic label - UC-EMLP (60X30) YE - 0822657

Accessories

Ink cartridge - BLUEMARK CLED-FLUID-CARTR. - 5146662



Cartridge, for replacement, 20 ml UV color, black, including cleaning cartridge

Ink cartridge - BLUEMARK FLUID-CARTRIDGE - 5147421



Cartridge, for replacement, 28 ml UV color, black including cleaning cartridge

Ink cartridge - BM ID-CARTR. BK - 1044345



Replacement UV fluid, 23 ml, color: black

Ink cartridge - BM ID-CARTR. CY - 1044346



Replacement UV fluid, 23 ml, color: cyan

Ink cartridge - BM ID-CARTR. MA - 1044347



Replacement UV fluid, 23 ml, color: magenta

Plastic label - UC-EMLP (60X30) YE - 0822657

Accessories

Ink cartridge - BM ID-CARTR. YE - 1044348



Replacement UV fluid, 23 ml, color: yellow

Phoenix Contact 2021 © - all rights reserved
<http://www.phoenixcontact.com>