

Connectors

- > Customer specific solutions
- > D SUB
- > D SUB cover
- > D SUB accessories
- > DVI
- > Centronics
- > IDC
- > Modular
- > USB
- > IEEE 1394
- > Switches
- > Power supply
- > DIN 41612
- > DIN 41617
- > Mini DIN
- > IC Socket
- > **Pin and female header**
- > Jumper
- > Connector sleeves
- > Solder terminals
- > Test terminals
- > Terminal Blocks
- > Memory Card connectors
- > FFC / FPC connectors
- > Micro-Miniature

Thermal management

Cable assembly



Pin and female header

AWL254-DG-G04D
female-header 02pins SMT 1,27mm 1A single row straight Sn

Article number: ABL127 E G Z 02 M P 1

product group: pin-&female-header

style: female-header

contact type: SMT

pin count: 2

spacing in mm: 1,27

current rating: 1A

version: single row

contact direction: straight

plating: Sn

contact machining: stamped contacts

packaging: tube

process: SMT

insulator: PA6T UL94V-0

: AWL254-DG-G04D

: #NV

» PDF download «

