



Part Number : [936013296](#)

Product Description : Heavy-Duty Standard-High Voltage (STD-HV) Double Lever Hood, Die-cast Aluminum, with 2 Levers, Side Entry, Size 24B «104x27», Pg21 Thread, Grey

Series Number : 93601

Status : Active

Product Category : Heavy-Duty Connectors

Engineering Number : 7824.5098.2



Documents & Resources

Drawings

[936013296_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Standard-High Voltage (STD-HV) Double Lever Hood, Die-cast Aluminum, with 2 Levers, Side Entry, Size 24B «104x27», Pg21 Thread, Grey
Component Type	Double Lever Hood
IP Rating	IP66
Product Name	Heavy-Duty Connectors
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD-HV
UPC	887191882390

Agency

CSA	256883
UL	E249674

Electrical

Voltage - Maximum	830V
-------------------	------

Physical

Color - Cable Jacket	N/A
Component Size	24B «104X27»
Entry Location	Side
Hood Coating	Polyester Powder
Hood Color	GREY RAL 7037
Lock to Mating Part	Yes
Material - Hood	Die-cast Aluminum

Material - Lever	Galvanized Steel
Net Weight	268.000/g
Number of Levers	2
Packaging Type	Bag
Thread Size	Pg21
Thread Type	(Pg)

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Size 24B «104x27» , S-EHV Inserts with Screw Terminals and S-HSB Inserts

This document was generated on Sep 18, 2025