Datasheet for part number KPTC6E8-4S-D-DZ-MB

Our Catalog Part Number: KPTC6E8-4S-D-DZ-MB
Our Global Manufacturing Part Number: 121659-5644
Brand: Cannon Product Category: Circular Product Line: 26482 - Style Series I & Mil Battery Series: KPTC

Product Datasheet	
Shell Style	Straight plug
Endbell Style	Endbell for shielding braids and shrink boots
Gender	Socket
Shell Size	8
Contact Arrangement	8-4
Number of contacts	4 contacts size 20
Contact Type	Crimp contacts (not assembled - packed separately)
Contact Plating	Size 12 & 16: gold plated Size 20: Contact body: tin / Contact area: gold plated
Shell Material	Aluminium alloy
Shell Plating	Olive drab chromate over cadmium plating
Insulator and Gromet Material	Polychloroprene
Contact Material	Copper alloy
Water Tightness	Acc. To VG95319 Part 2, Test No. 5.9.2
Operating Temperature	-55°/+125°C (-67/257°F)
Mating Cycles	500 min
Vibration	200 m/s² at 10 to 2000 Hz
Contact Rating AWG20	7,5 A
Insulator Resistance	≈5000 MOhm
Test Voltage	1500 Vrms
Operating Voltage	In case of voltages greater than 50V the connector must be used in accordance with DIN VDE part 410, IEC 60364-4-41.
Safety Provisions	IP67 acc. to DIN 40 050 (0,2 bar pressure over 48 hrs)
Salt Spray Resistance	500 hours salt spray resistant
General Info	*All tests in accordance with VG95319 and/or if applicable with VG95210*
Harnessing Info: Contact Cross-Section	See assembly instruction
Harnessing Info: Insulator Diameter	See assembly instruction

Specifications and dimensions subject to change.

Downloaded from Arrow.com.