

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)



Always EU RoHS/ELV Compliant (Statement of Compliance)

? Power Generation and Distribution
Application
? Wire Size (AWG/CM) = 350,000 CM
? Wire Range = 325000 - 375000 CMA
? Terminal Type = Standard
? 0 Holes

[View all Features](#) | [Find Similar Products](#)

[? TERMINAL, AMPPOWER, WIRE SIZE: 350 MCM](#) (PDF, English)

? None Available

? None Available

? None Available

? None Available

? None Available

? Product Line Information

? Tooling

List all Documents

? Terminal Type = Standard
 ? Material = Copper (Annealed) per ASTM B -75
 ? Body Style = Straight
 ? Tongue Material Thickness (mm [in]) = 4.32
 [0.170]
 ? Finish = None
 ? Comment = Cleaned but not plated.

? Wire Size (AWG/CM) = 350,000 CM

? Wire Range (CMA) = 325,000 – 375,000

? Number of Holes = 0

? Barrel I.D. Min. (mm [in]) = 20.80 [0.819]

? Barrel Length = Standard

? Inspection Slot = With

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

? Application = Power Generation and Distribution

? Packaging Quantity = 25

? Brand = AMP