

Part Number : 03091042
Product Description : 2.36mm Diameter Standard .093" Pin and Socket Receptacle Housing, 4 Circuits, Single Row, Natural
Series Number : 1490
Status : Active
Product Category : Connector Housings
Engineering Part Number : 1490-R1

Documents and Resources

Drawings

003091042_sd.pdf

PK-1490-001-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-02-09-001.pdf

PS-43660-9999-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	1490
Description	2.36mm Diameter Standard .093" Pin and Socket Receptacle Housing, 4 Circuits, Single Row, Natural
Application	Wire-to-Wire
Comments	14.0A max. can be achieved when housing is used with 42477 or 42478 terminals
Component Type	Receptacle
Product Name	Standard .093"
UPC	800753615090

Agency

CSA	LR19980
UL	E29179

Physical

Circuits Detail	(1 x 4)
Circuits (maximum)	4
Color - Resin	Natural
Flammability	94V-2

Downloaded from Arrow.com.

Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	2.179/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.03mm
Pitch - Termination Interface	5.03mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.36mm Diameter Standard .093" Pin and Socket Plug Housing, 4 Circuits, Single Row	03092041
2.36mm Diameter Standard .093" Pin and Socket Plug Housing, 4 Circuits, Single Row	03092042
Standard .093" Pin and Socket Vertical Headers	3099

Use with Part(s)

Description	Part Number
Standard .093" Pin and Socket Female Crimp Terminals	1189
Standard .093" Pin and Socket Male Crimp Terminals	1190
Standard .093" Pin and Socket Male Crimp Terminals	1380
Standard .093" Pin and Socket	1381

Downloaded from Arrow.com.

Female Crimp Terminals	
Standard .093" Pin and Socket Male Crimp Terminal	1434
Standard .093" Pin and Socket Male Crimp Grounding Terminals	1973

Downloaded from Arrow.com.