

Part Number: **5510407100F**

General Description	
Series	551
Configuration	3 mm Lens
Description	3 mm CBI Right Angle
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Single Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Tinted, Diffused
Viewing Angle	45
LED Centerline	5.0mm

Absolute Maximum Ratings (Ta = 25Â°)	
Derating	0.5 (mA/degC)
Reverse Voltage	3
Solder Temperature	260 for 5 secs
Operating Temperature	-25 to +85
Storage Temperature	-30 to +100

Operating Characteristics	
Color	Red
LED Type	Standard Efficiency
Peak Wave Length	650
Luminous Intensity Min	3.6
Luminous Intensity Typical	10
Forward Voltage Typical	2
Forward Voltage Max	3
Test Current mA	20mA
Power Dissipation Max	60mW



5510407100F

check stock



[This is a RoHS Compliant Product](#)
[To learn more click here](#)