

3-2061348-5 Product Details

Share Print Email



Active

Fiber Optic Cable Assemblies

FOSM LEAD LC/DPX ODVA - LC/DPX 35M

3-2061348-5

TE Internal Number: 3-2061348-5

Product Highlights View All

- Duplex Fiber
- Cable Assembly
- LC Fiber Optic Cable Connector Type, LC with ODVA Adapter Fiber Optic Cable Connector Type
- Fiber Type = 9/125 Micron
- Cable Assembly Type = LC Duplex to LC Duplex

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Feedback

Documents Features Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Product Designation	Duplex Fiber
Product Type	Cable Assembly
Fiber Optic Cable Connector Type	LC, LC with ODVA Adapter
Cable Assembly Type	LC Duplex to LC Duplex
Cable Type	FOCAB ODC™

Termination Features	
Fiber Type (Micron)	9/125

Dimensions	
Cable Diameter (mm [in])	5.50 [.216]
Length (M [ft])	35.00 [114.83]

Body Features	
Cable Color	Black
Connector Color	Blue
Boot Body Style - Left	Standard
Boot Color - Left	Black
Boot Body Style - Right	Standard
Boot Color - Right	Blue
Protective Cap	With

Contact Features	
Fibre Channel	No

Configuration Features	
Mode	Singlemode
Number of Fibers	2
Cable Buffering	Tight Buffered
Connector(s) Exit Angle to Connector(s) Exit Angle	180° to 180°

Industry Standards	
RoHS/ELV Compliance	ELV compliant, RoHS compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Product Availability	
Region	Not Specified

Other	
Brand	TE Connectivity

Related Products

Not quite the product you're looking for?
Find Similar Products

View Part in Product Feature Selector

Check for Tooling