

NTE5010T1 thru NTE5021T1 Zener Diode, 500mW ±1% Tolerance

Features:

- Zener Voltage 5.1V to 12V
- Constructed with an Oxide Passivated All Diffused Die
- DO35 Type Axial Lead Package

Absolute Maximum Ratings:

Forward Voltage ($I_F = 100\text{mA}$, $T_L = +30^\circ\text{C}$, Lead Length = 3/8"), V_F 1.5V
 DC Power Dissipation ($T_L \leq +50^\circ\text{C}$, Lead length = 3/8"), P_D 500mW
 Derate Above 50°C 3.33mW/ $^\circ\text{C}$
 Operating Temperature Range, T_{opr} -65°C to $+200^\circ\text{C}$
 Storage Temperature Range, T_{stg} -65°C to $+200^\circ\text{C}$

Electrical Characteristics: ($T_L = +30^\circ\text{C}$, Lead Length = 3/8" unless otherwise specified)

NTE Type Number	Nom Zener Voltage (Note 1) $V_Z @ I_{ZT}$	Zener Test Current (I_{ZT})	Max DC Zener Current (Note 2) (I_{ZM})	Max Zener Impedance (Note 3)		Typical Temperature Coefficient α_{VZ}	Max Leakage Current $I_R @ V_R$	
				$Z_{ZT} @ I_{ZT}$	$Z_{ZK} @ 0.25\text{mA } (I_{ZK})$			
	Volts	mA	mA	Ohms	Ohms	%/ $^\circ\text{C}$	μA	Volts
5010T1	5.1	5	98	50	2050	+0.025	2.0	2.0
5011T1	5.6	5	89	25	1800	+0.035	2.0	3.0
5013T1	6.2	5	81	10	1300	+0.040	1.0	4.0
5019T1	10.0	5	50	15	600	+0.065	0.1	8.0
5021T1	12.0	5	42	22	600	+0.073	0.1	9.1

Note 1. Voltage measurement to be performed 20 seconds after application of the DC test current.

Note 2. The maximum zener current (I_{ZM}) shown is for the nominal voltages. The following formula can be used to determine the worst case current for any tolerance device:

$$I_{ZM} = \frac{P}{V_{ZM}}$$

Where V_{ZM} is the high end of the tolerance specified and P is the rated power of the device.

Note 3. Zener impedance is derived from the 1kHz AC voltage which results when an AC current having an RMS value equal to 10% of DC zener current (I_{ZT} or I_{ZK}) is superimposed on I_{ZT} or I_{ZK} .

