



C2G
Discontinued - Brocade® XBR-000147 Compatible 8Gbs Fiber Channel SW SFP+ Transceiver Module (Multimode, 850nm, 300m, LC)
Part No. XBR-000147-LEG



This Brocade® XBR-000147 compatible SFP+ transceiver provides 8Gbs Fiber Channel-SW throughput up to 300m over multi-mode fiber (MMF) at a wavelength of 850nm using a LC connector. It is guaranteed to be 100% compatible with the equivalent Brocade® transceiver. This easy to install, hot swappable transceiver has been programmed, uniquely serialized and data-traffic and application tested to ensure that it will initialize and perform identically. It is built to meet or exceed the specifications of Brocade®, as well as to comply with MSA (Multi-Source Agreement) standards to ensure seamless network integration. All Legrand transceivers are Trade Agreements Act (TAA) compliant.

Features & Benefits	
Supports data rates up to 8Gbps	SFP+ transceiver module
LC ports designed for use with Multimode Fiber	850nm wavelength signaling
Supports up to 300 meters of cabling	

Specifications			
General Info			
Product Line	C2G	Color	Silver
UPC Number	757120669036	Country Of Origin	United States
Application Sector	Commercial, Industrial	Type	Transceiver

Technical Information			
Fiber Optic Cable Type	Multimode	Max Distance Support	300 m
Connector 1	SFP+ Male		