



UNCONTROLLED DOCUMENT



PART NUMBER		REV.
SSL-LX5093SRC(/B-/E)-TR		B
REV.	E.C.N. NUMBER AND REVISION COMMENTS	DATE
A	REDRAWN AND UPDATED SPECS./	2.13.95
B	E.C.N. #11148.	02.05.07

ELECTRO-OPTICAL CHARACTERISTICS TA=25 °C				I _f =20mA
PARAMETER	MIN	TYP	MAX	UNITS TEST COND
PEAK WAVELENGTH		660 (RED)		nm
FORWARD VOLTAGE		1.7	2.2	V _f
REVERSE VOLTAGE	4.0			V _r I _r =100uA
AXIAL INTENSITY	/B	500		mcd I _f =20mA
	/C	500	1000	mcd I _f =20mA
	/DU	1000	1300	mcd I _f =20mA
	/DV	1300	1600	mcd I _f =20mA
	/DW	1600	2000	mcd I _f =20mA
	/E	2000	3500	mcd I _f =20mA
VIEWING ANGLE		30 DEG		2x theta
EMITTED COLOR :		SUPER RED		
EPOXY LENS FINISH:		WATER CLEAR		

LIMITS OF SAFE OPERATION AT 25 DEG. C		
PARAMETER	MAX	UNITS
PEAK FORWARD CURRENT *	150	mA
STEADY CURRENT	30	mA
POWER DISSIPATION	100	mW
DERATE FROM 25 °C	-1.3	mW/°C
OPERATING, STORAGE TEMP.	-40 TO +85	°C
LEAD SOLDERING TEMP.	+260	°C
2.0mm FROM BODY		3 SEC. MAX
* t<10uS		

*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.038), XX=±0.5 (±0.020), XXX=±0.25 (±0.010), XXXX=±0.127 (±0.005). LEAD SIZE=±0.05 (0.002), LEAD LENGTH=±0.75 (±0.030). MIN= +DECIMAL PRECISION MAX= +0.00 -DECIMAL PRECISION

REV.	PART NUMBER
B	SSL-LX5093SRC(/B-/E)-TR

T-5 (T 1-3/4) LED, SUPER BRIGHT RED,
WATER CLEAR LENS, TAPE AND REEL.

CONFIDENTIAL INFORMATION
THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

RELIABILITY NOTE
OUR MANY YEARS OF EXPERIENCE DATA ACCUMULATION INDICATE THAT SOLDER HEAT IS A MAJOR CAUSE OF EARLY AND FUTURE FAILURE. PLEASE PAY ATTENTION TO YOUR SOLDERING PROCESS.



290 E. HELEN ROAD
PALATINE, IL 60067-6976
PHONE: +1.847.359.2790
US WEB: www.lumex.com
TW WEB: www.lumex.com.tw

DRAWN BY:	CHECKED BY:	APPROVED BY:	DATE: 11.30.93
JC			PAGE: 1 OF 1
			SCALE: N/A



UNCONTROLLED DOCUMENT