


961-004 TURBOFLEX, .032" WALL, 2000 VAC

How to Order TurboFlex®					
Sample Part Number	961	-004	-T	-G	-2
Basic No.	TurboFlex with Duraelectric D Jacket				
Wall Thickness	-004 = .032"				
Conductor Material	-T = Tin/Copper (-60 – 150°C) -S = Silver/Copper (-60 – 200°C) -N = Nickel/Copper (-60 – 260°C)				
Wire Size (See Table I)	T, R, S, A, B, C, D, E, F, G				
Duraelectric D Jacket Color	See Table II				



Voltage Ratings		
P/N	AC Voltage Rating, RMS	DC Voltage Rating
961-004	2000	2800

Table I: TurboFlex Wire Size, Dimensions, DC Resistance and Ampacity Ratings									
AWG Code	AWG	Strand / Count / AWG	Cir Mil (nom)	Ø B in. (mm)	DC Resistance @ 20°C (Ohms / 1000 ft.)			Ampacity (Amps) 40°C Ambient	
					Nickel Copper	Tin Copper	Silver Copper	Nickel Copper	Tin/Silver Copper
T	20	42-36	1050	.037 (.94)	10.7178	10.7538	10.0747	16	14
R	16	7 X 15/36	2625	.063 (1.60)	4.5510	4.5930	4.2780	40	36
S	14	7 X 24/36	4200	.080 (2.03)	2.8450	2.8710	2.6740	59	54
A	12	7 X 37/36	6475	.099 (2.51)	1.8450	1.8620	1.7340	78	68
B	10	7 X 59/36	10325	.126 (3.20)	1.1570	1.1680	1.0880	107	90
C	8	7 X 95/36	16625	.159 (4.04)	.7188	.7252	.6755	142	124
D	6	7 X 150/36	26250	.200 (5.08)	.4551	.4593	.4278	205	165
E	4	7 X 7 X 34/36	41650	.271 (6.88)	.2979	.3006	.2800	278	220
F	2	7 X 7 X 54/36	66150	.342 (8.69)	.1876	.1893	.1763	381	293
G	1/0	7 X 7 X 86/36	105350	.431 (10.95)	.1178	.1188	.1107	532	399

Table II: Duraelectric™ D Jacket Color		
Weatherproof, halogen free, flame resistant, functional to 260°C		
0	Black	Fed-Std-595C #17038
1	Brown	[TBD]
2	Red	Fed-Std-595C #11120
3	Orange	Fed-Std-595C #12300
4	Yellow	Fed-Std-595C #13591
5	Kelly Green	Fed-Std-595C #14193
6	Blue	Fed-Std-595C #15125
7	Violet	Fed-Std-595C #17142
8	Gray	Fed-Std-595C #26270
9	White	Fed-Std-595C #17875
OG	Dark Olive Green	Fed-Std-595C #34094
DT	Desert Tan	Fed-Std-595C #33446
Consult factory for other specific Fed Std colors		

961-004 Wire Weight and Outer Diameter			
AWG Code	Weight lbs/1000 ft. (nom.)	Ø A in. (mm)	Jacket wall thickness in. (mm)
T	7.60	.101 (2.57)	.032 (.81)
R	14.40	.127 (3.23)	
S	20.70	.144 (3.66)	
A	29.40	.163 (4.14)	
B	43.90	.190 (4.83)	
C	66.90	.223 (5.66)	
D	101.40	.264 (6.71)	
E	162.40	.335 (8.51)	
F	251.60	.406 (10.31)	
G	392.70	.495 (12.57)	

NOTES

1. Bend radius is 3X the outer diameter
2. Cable will be marked with "GLENAIR TURBOFLEX", wire gauge, part number, CAGE 06324.
3. Jacket thickness tolerance is ±.005