

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0350211301

Status:

Active

Overview:

Board-in Connectors

Description:

2.00mm Pitch, Board-in Male Crimp Terminal, Right-Angle, Pre-Plated, 24-30 AWG, Reel

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	35021
Application	Signal, Wire-to-Board
Comments	Right-angle, Use with housing 35023
Crimp Quality Equipment	Yes
Overview	Board-in Connectors
Product Name	Board-in
UPC	800753576933
Physical	
Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.031/g
Packaging Type	Reel
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.50mm max.
Wire Size AWG	24, 26, 28, 30
Wire Size mm²	N/A
Electrical	
Current - Maximum per Contact	2.0A
Voltage - Maximum	125V AC (RMS)/DC

Material Info



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)4578-DC (25 June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

35021 Series

Use With

35023

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool for Right-Angle Board-in Crimp Terminals	638116900
FineAdjust Applicator for Right-Angle 2.00mm (.079") Board-in-Terminals	639029000
T2 Terminator for Right-Angle, 2.00mm (.079") Board-in Terminals	639129000

This document was generated on 10/30/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION