



Connectors > Sockets > Pin Sockets

2-5332070-9 ✓ ACTIVE

3.63 mm [.143 in] Socket Length, 1.83 mm [.072 in] PCB Hole, Open Bottom, .653 mm² Wire, 19 AWG, Cable-to-Board, Power & Signal, Pin Sockets



TE Internal #: 2-5332070-9
TE Internal Description: SOCKET,MIN-SPR W/ H SN-AU SER-4

Socket Length : 3.63 mm [.143 in]
PCB Hole Diameter : 1.83 mm [.072 in]
Socket Sleeve Style : Open Bottom
Wire Size (AWG): 19
Wire Size (mm²): .653

Add to List | Get Free Samples

[Similar Products](#)

[Compatible Parts & Tooling](#)

We are here to help!
Get in touch with our product experts.

[CHAT WITH US](#)

[EMAIL US](#)

[CALL US](#)

Documents	Features	Product Compliance
Product Drawings	MINIATURE SPRING SOCKET ASSEMBLY SERIES 4 ENG_CD_5332070_A1.Pdf English	
CAD Files	3D PDF 3D_CVM_CVM_2-5332070-9_A.pdf 3D Customer View Model ENG_CVM_CVM_2-5332070-9_A.2d_dxf.zip English ENG_CVM_CVM_2-5332070-9_A.3d_igs.zip English ENG_CVM_CVM_2-5332070-9_A.3d_stp.zip English	
Product Specifications	Product Specification ENG_SS_108-14008_H_108-14008.pdf English	

Feedback

Product Change Notification

View Product Change Notification

Login required to access product change notifications

REPORT PRODUCT DATA ERROR

Compatible Parts

Filter By Specification



ASSOCIATED

2-5332070-8

3.63 mm [.143 in] Socket Length,
1.83 mm [.072 in]...

Non-Stocked

VIEW PRODUCT



ASSOCIATED

3-5332070-5

3.63 mm [.143 in] Socket Length,
1.83 mm [.072 in]...

From: 0.833
In-Stock

ADD TO CART



ASSOCIATED

2-5332070-3

3.63 mm [.143 in] Socket Length,
1.83 mm [.072 in]...

From: 1.021
In-Stock

ADD TO CART

Products with Similar Specs

View All Similar Products

THIS PRODUCT

PIN SOCKETS

2-5332070-9

3.63 mm [.143 in] Socket Length,
1.83 mm [.072 in] PCB Hole, Open...



From \$0.998

In-Stock 

Socket Length : 3.63 mm

PCB Hole Diameter : 1.83 mm

Socket Sleeve Style : Open Bottom

Wire Size : 19 AWG

Wire Size : .653 mm²

Top Results ?

PIN SOCKETS

1-332070-3

3.63 mm [.143 in] Socket Length,
1.83 mm [.072 in] PCB Hole, Open...



In-Stock

Socket Length : 3.63 mm

PCB Hole Diameter : 1.83 mm

Socket Sleeve Style : Open Bottom

Wire Size : 20 – 19 AWG

Wire Size : .518 – .653 mm²

PIN SOCKETS

1-50865-2

6.6 mm [.26 in] Socket Length, 1.83
mm [.072 in] PCB Hole, Open



Non-Stocked

Socket Length : 6.6 mm

PCB Hole Diameter : 1.83 mm

Socket Sleeve Style : Open Bottom

Wire Size : 20 – 18 AWG

Wire Size : .518 – .823 mm²

PIN SOCKETS

5050865-3

6.6 mm [.26 in] Socket Length, 1.83
mm [.072 in] PCB Hole, Open



From \$0.695

In-Stock 

Socket Length : 6.6 mm

PCB Hole Diameter : 1.83 mm

Socket Sleeve Style : Open Bottom

Wire Size : 20 – 18 AWG

Wire Size : .518 – .823 mm²

Customers Also Bought



TE Part #: **5-103669-2**
PCB Mount Header, Vertical,
3 Position, 2.54 mm [0.1 in]...

\$1.598 per unit
Inventory: In-Stock

[Add To Cart](#)



TE Part #: **5-103908-2**
PCB Mount Header, Vertical,
3 Position, 2.54 mm [0.1 in]...


[View Product](#)



TE Part #: **FCA-410-1620M**
General Purpose Power
Relay, DC, Polarized...

\$400.000 per unit
Inventory: In-Stock

[Add To Cart](#)



TE Part #: **1-1761609-5**
Wire-to-Board, 50 Position,
2.54 mm [0.1 in] Centerline...

[View Product](#)