Specifications



Photo is representative





Eaton DR73-680-R

Eaton DR73 inductor, 68uH, 0.89A Irms, 0.96A ISAT, 418mOhm resistance, SMT mounting, Ferrite, 2-pins, 1350 qty.

General specifications	
PRODUCT NAME	Eaton DR73 inductor
CATALOG NUMBER	DR73-680-R
UPC	051712888790
EAN	5027590129381
PRODUCT LENGTH/DEPTH	7.6 mm
PRODUCT HEIGHT	3.55 mm
PRODUCT WIDTH	7.6 mm
PRODUCT WEIGHT	0.609 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	0.89 A
ISAT	0.96 A
PACKAGE QUANTITY	1350
MATERIAL	Ferrite
AUTOMOTIVE GRADE	No
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	418 mΩ
TERMINALS	7.5x7.5x3.35mm
SERIES	DR73

Resources

SPECIFICATIONS AND DATASHEETS	Eaton DR high power density high efficiency shielded drum core power inductors data sheet Eaton Specification Sheet - DR73-680-R

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2026 Eaton. All Rights Reserved.

Downloaded from Arrow.com.