



Part Number : 1722563103

Series Number : 172256

Product Category : Connector Housings

Product Description : Ultra-Fit Tangless
Receptacle Housing, 3.50mm Pitch, Single
Row, 3 Circuits, Black, Glow-Wire Capable

Status : Active

Documents & Resources

Drawings

Drawing 1722563103_sd.pdf

Packaging Design Drawing 1723230004-000.pdf

3D Models and Design Files

3D Model 1722563103_stp.zip

Specifications

Application Specification 1723230003-000.pdf

Product Specification 1723230001-TS-000.pdf

Product Specification 1723231000-PS-CH-000.pdf

Product Specification 1723231000-PS-ES-000.pdf

Product Specification 1723231000-PS-JP-000.pdf

Product Specification 1723231000-PS-SK-000.pdf

Product Specification PS-172323-0001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	172256
Description	Ultra-Fit Tangless Receptacle Housing, 3.50mm Pitch, Single Row, 3 Circuits, Black, Glow-Wire Capable
Application	Power, Wire-to-Board
Product Family	Ultra-Fit Power Connectors
Product Name	Ultra-Fit
UPC	191130133819

Physical

Circuits (maximum)	3
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.253/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Polarized to Mating Part	Yes

Temperature Range - Operating	-40° to +105°C
-------------------------------	----------------

Mates With / Use With

Mates with Part(s)

Description	Part Number
Ultra-Fit Vertical Header, 3.50mm Pitch, Single Row, 3 Circuits, with Kinked Pins, Tin (Sn), Glow-Wire Capable, Black	<u>1722861103</u>
Ultra-Fit Vertical Header, 3.50mm Pitch, Single Row, 3 Circuits, with Kinked Pins, 0.38µm Gold (Au) Plating, Glow-Wire Capable, Black	<u>1722861203</u>
Ultra-Fit Vertical Header, 3.50mm Pitch, Single Row, 3 Circuits, with Kinked Pins, 0.76µm Gold (Au) Plating, Glow-Wire Capable, Black	<u>1722861303</u>
Ultra-Fit Vertical Header, 3.50mm Pitch, Single Row, 3 Circuits, with Solder Clips, Tin (Sn), Glow-Wire Capable, Black	<u>1722871103</u>
Ultra-Fit Vertical Header, 3.50mm Pitch, Single Row, 3 Circuits, with Solder Clips, 0.38µm Gold (Au) Plating, Glow-Wire Capable, Black	<u>1722871203</u>
Ultra-Fit Vertical Header, 3.50mm Pitch, Single Row, 3 Circuits, with Solder Clips, 0.76µm Gold (Au) Plating, Glow-Wire Capable, Black	<u>1722871303</u>
Ultra-Fit Right-Angle Header with Solder Nail, 3.50mm Pitch, Single Row, 3 Circuits, Tin (Sn) Plating, Black, Glow-Wire Capable	<u>1723103103</u>
Ultra-Fit Right-Angle Header with Solder Nail, 3.50mm Pitch, Single Row, 3 Circuits, 0.38µm Gold (Au) Plating, Black, Glow-Wire Capable	<u>1723103203</u>
Ultra-Fit Right-Angle Header with Solder Nail, 3.50mm Pitch, Single Row, 3 Circuits, 0.76µm Gold (Au) Plating, Black, Glow-Wire Capable	<u>1723103303</u>
Ultra-Fit Plug Housing, 3.50mm Pitch, Single Row, 3 Circuits, Black, Glow-Wire Capable	<u>2025693003</u>
Ultra-Fit Plug Housing, 3.50mm Pitch, Single Row, 3 Circuits, Panel Mount, Black, Glow-Wire Capable	<u>2025693103</u>

Use with Part(s)

Description	Part Number
Ultra-Fit Tangless Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 16-18 AWG	/content/molex/molex-dot-com/us/en/products/product-page.html/1722536011.html
Ultra-Fit Tangless Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 20-22 AWG	/content/molex/molex-dot-com/us/en/products/product-page.html/1722536111.html
Ultra-Fit Tangless Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 16-18 AWG	/content/molex/molex-dot-com/us/en/products/product-page.html/1722536012.html
Ultra-Fit Tangless Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 20-22 AWG	/content/molex/molex-dot-com/us/en/products/product-page.html/1722536112.html
Ultra-Fit Tangless Crimp Terminal, Female, Tin (Sn) Plating, 16-18 AWG	/content/molex/molex-dot-com/us/en/products/product-page.html/1722537023.html
Ultra-Fit Tangless Crimp Terminal, Female, Tin (Sn) Plating, 20-22 AWG	/content/molex/molex-dot-com/us/en/products/product-page.html/1722537123.html
Pre-Crimped Lead Ultra-Fit Tangless-Female-to-Ultra-Fit Tangless Female, Tin (Sn) Plating, 150.00mm Length, 16 AWG, Black	/content/molex/molex-dot-com/us/en/products/product-page.html/797582141.html
Pre-Crimped Lead Ultra-Fit Tangless-Female-to-Ultra-Fit Tangless Female, Tin (Sn) Plating, 300.00mm Length, 16 AWG, Black	/content/molex/molex-dot-com/us/en/products/product-page.html/797582142.html
Ultra-Fit Tangless Terminal Position Assurance (TPA), 3.50mm Pitch, 3 Circuits, Natural	/content/molex/molex-dot-com/us/en/products/product-page.html/1722644003.html

This document was generated on Aug 31, 2024