

## 2 - 324463 - 5 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**2 - 324463 - 5**

TE Part Number: 2 - 324463 - 5

**Active**

[Add to Part List](#)

### AMPOWER Splices

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Splice Type = Butt
- ? Wire Size (AWG/CM) = 300,000 CM
- ? Barrel Length = Standard
- ? Barrel I.D. Min. = 19.51 mm

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [SPLICE, BUTT, AMPOWER WIRE SIZE: 300 MCM](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features

(Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? Splice Type = Butt
- ? Finish = Tin
- ? Material = Copper (Annealed) per ASTM B -75
- ? Comment = Tin Plate per ASTM B -545

#### Body Related Features:

- ? [Wire Size \(AWG/CM\)](#) = 300,000 CM
- ? [Barrel Length](#) = Standard
- ? [Barrel I.D. Min. \(mm \[in\]\)](#) = 19.51 [0.768]
- ? Wire Range (CMA) = 275,000 - 325,000

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Other:

- ? Brand = AMP