

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → Solution Series

General Information

Extended Product Type:	M4/9.PV24/15
Product ID:	1SNA007007R2600
EAN:	3472590070072
Catalog Description:	M4/9.PV24/15 Screw Clamp Terminal Blocks - Component holder - Grey
Long Description:	M4/9.PV24/15 Screw Clamp Terminal Blocks Surge protection.

Ordering

Color:	grey
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85371098

Popular Downloads

Data Sheet, Technical Information:	1SNC110001C0203_Ch_A
Instructions and Manuals:	1SNC110001C0203_Ch_A

Dimensions

Product Net Width:	9 mm
Product Net Height:	65.5 mm
Product Net Depth / Length:	52 mm
Product Net Weight:	0.02 kg

Technical

Spacing:	9 mm
Connection Type:	Screw clamp
Function:	Surge protection

Technical UL/CSA

Flammability According to UL94:	V2
--	----

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225050U1000
Environmental Information:	1SND220007E1000
Instructions and Manuals:	1SNC110001C0203_Ch_A
RoHS Information:	1SND230023F0201

Classifications

Object Classification Code:	X
ETIM 4:	EC000903 - Component terminal block
ETIM 5:	EC000903 - Component terminal block
ETIM 6:	EC000903 - Component terminal block

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	85 mm
Package Level 1 Depth / Length:	110 mm
Package Level 1 Height:	60 mm
Package Level 1 Gross Weight:	0.2 kg
Package Level 1 EAN:	3472590070072
Package Level 2 Units:	200 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	500 mm
Package Level 2 Height:	150 mm
Package Level 3 Units:	9600 piece
Product Packing Type:	Box

