



Part Number : [1054390005](#)

Product Description : Anti-Snag Spring Clip,
1.32mm Width, 0.25µm Gold (Au) Plating, 1.40mm
-2.00mm Working Range (Height)

Series Number : 105439

Status : Active

Product Category : Connector Accessories



Documents and Resources

Drawings

[1054390005_sd.pdf](#)

[PK-105439-001-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-105439-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	105439
Description	Anti-Snag Spring Clip, 1.32mm Width, 0.25µm Gold (Au) Plating, 1.40mm -2.00mm Working Range (Height)
Component Type	Clip
Product Name	Spring Clip
UPC	889056318648

Electrical

Current - Maximum per Contact	1.5A
-------------------------------	------

Physical

Circuits (Loaded)	1
Circuits (maximum)	1
Material - Metal	Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.008/g
Packaging Type	Embossed Tape on Reel
Plating min - Mating	0.254µm

Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Solder

This document was generated on Apr 27, 2026