

External SAS Cable, 4 Lane - 4xInfiniband (SFF-8470) to 4xInfiniband (SFF-8470), 3M (9.84 ft.), TAA

MODEL NUMBER: **S522-03M**



Highlights

- Hi-Performance 3 Meter SAS External Cable
- SFF-8470 to SFF-8470
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- SAS Controllers, SAS Chassis, SAS/SATA hard Drives

Package Includes

3 Meter SAS External SFF-8470 to SFF-8470 Cable

Features

- External SAS Cable, SFF-8470 to SFF-8470 - 3 Meter
- Made with High Performance Infiniband Cable
- Support data transfer rates from 3.0 up to 6.0 gigabytes per second
- SFF-8470 thumbscrew type connectors in diecast zinc housing for durability
- RoHS compliant
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332151988
Technology	SAS
CONNECTIONS	
Side A - Connector 1	SFF-8470
Side B - Connector 1	SFF-8470
PHYSICAL	
Color	Black
Cable Length (ft.)	9.8
Cable Length (m)	2.99



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / in.)	12.20 x 9.80 x 0.50
Shipping Dimensions (hwd / cm)	30.99 x 24.89 x 1.27
Shipping Weight (lbs.)	0.83
Shipping Weight (kg)	0.38
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.