

Part Number : [1300980195](#)

Product Description : MAX-LOC Multi-Hole Strain Relief, 1/2" NPT, Straight Male, Cable Diameter 5.72mm (.225")

Series Number : 130098

Status : Active

Product Category : Cable Grips

Engineering Part Number : 5594-004



Documents and Resources

Drawings

[1300980195 sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Multi-Hole Strain Relief, 1/2" NPT, Straight Male, Cable Diameter 5.72mm (.225")
Comments	Indicates that one or more grommet hole is covered by a thin membrane which can easily be "Poked" open if required.
NEMA Rating	NEMA 3R
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678850409

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	5.72mm (.225")
Color - Grommet	Yellow
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Number of Holes	2, 3, or 4
O-Ring	No

Thread Size	1/2" NPT
-------------	----------

Mates With / Use With

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1/2" NPT	<u>1300990143</u>
MAX-LOC Gasket Sealing Ring, 1/2" NPT, Black	<u>1300990149</u>
MAX-LOC O-Ring, 1/2" NPT	<u>1301800314</u>

This document was generated on Dec 29, 2025