

Universal Reversible USB 2.0 Cable (Right / Left-Angle Reversible A to B M/M), 3 ft. (0.91 m)

MODEL NUMBER: UR022-003-RA



Reversible Right / Left Angle USB "A" connector plugs in any direction

Description

Tripp Lite's UR022-003-RA, 3-ft. (0.91 m) USB2.0 Right / Left Angle "A" to B device cable, with Universal / Reversible "A" connector, meets or exceeds USB 2.0 specifications. No guessing on how to plug into the Computer or Hub port... Connects in either direction. Backward compatible - can be used with older USB1.1 applications as well. All Tripp Lite USB 2.0 cabling include superior foil shielding for reliable, error-free data communications. The significantly faster data transfer rates of USB 2.0 (up to 480 Mbps) make them perfect for multimedia applications. Features nickel plated connectors and gold plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life.

Features

- 3-ft. (0.91 m), USB 2.0 Right / Left Angle A-Male to B-Male, with Universal / Reversible "A" connector
- USB 2.0 compliant, to 480Mbps transfer rates
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 28AWG Data Pair, 24AWG Power pair

Specifications

OVERVIEW	
UPC Code	037332179463
Technology	USB 2.0 (High Speed)
USB Cable Type	Passive
PHYSICAL	
Cable Jacket Color	Black

Highlights

- 3-ft. (0.91 m), USB 2.0, Right / Left Angle A to B Peripheral device cable
- Universal, Reversible "A" connector allows plugging in any direction

System Requirements

- Any USB device requiring a USB cable
- USB2.0 performance only when used with USB2.0 device and USB2.0 controller

Package Includes

- Universal Reversible USB 2.0 Right / Left Angle A-Male to B-Male Device Cable - 3-ft. (0.91 m)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	0.25 x 5.00 x 7.00
Shipping Dimensions (hwd / cm)	0.64 x 12.70 x 17.78
Shipping Weight (lbs.)	0.10
Shipping Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	14 to 122 F (-10 to 50 C)
Storage Temperature Range	5 to 140 F (-15 to 60 C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	USB B (MALE)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>