



Pushing Performance  
Since 1945

# SEK CAB FLAT NSH RND AWG28/7 34P 30,48m



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 18 034 7008                                                                |
| Specification      | SEK CAB FLAT NSH RND AWG28/7<br>34P 30,48m                                    |
| HARTING eCatalogue | <a href="https://harting.com/09180347008">https://harting.com/09180347008</a> |

## Identification

|               |                      |
|---------------|----------------------|
| Category      | System cabling       |
| Element       | Bulk cables          |
| Specification | Not assembled        |
| Type of cable | Copper cable (round) |

## Version

|                 |            |
|-----------------|------------|
| Cable length    | 30.48 m    |
| Number of cores | 34         |
| Core structure  | AWG 28/7   |
| Shielding       | Unshielded |

## Technical characteristics

|                                              |                                                                                |
|----------------------------------------------|--------------------------------------------------------------------------------|
| Impedance                                    | 100 $\Omega$                                                                   |
| Limiting temperature                         | -30 ... +75 $^{\circ}\text{C}$ unmoved<br>-20 ... +75 $^{\circ}\text{C}$ moved |
| Conductor resistance @ 20 $^{\circ}\text{C}$ | $\leq 216 \Omega/\text{km}$                                                    |

## Material properties

|                  |           |
|------------------|-----------|
| Material (cable) | PVC       |
| Colour (cable)   | Grey      |
| RoHS             | compliant |
| ELV status       | compliant |
| China RoHS       | e         |



**Pushing Performance**  
Since 1945

**Material properties**

|                                      |               |
|--------------------------------------|---------------|
| REACH Annex XVII substances          | Not contained |
| REACH ANNEX XIV substances           | Not contained |
| REACH SVHC substances                | Not contained |
| California Proposition 65 substances | Not contained |

**Specifications and approvals**

|                |              |
|----------------|--------------|
| Specifications | UL 1581      |
|                | UL PLCC, CL2 |
| Approvals      | CE           |

**Commercial data**

|                                |                                                |
|--------------------------------|------------------------------------------------|
| Packaging size                 | 1                                              |
| Net weight                     | 108 g/m                                        |
| Country of origin              | Germany                                        |
| European customs tariff number | 85444993                                       |
| GTIN                           | 5713140025059                                  |
| eCl@ss                         | 27061801 Data and communication cable (copper) |
| ETIM                           | EC003249                                       |
| UNSPSC 24.0                    | 26121609                                       |