

Junction FETs* (Continued)

Switches / Choppers

N-Channel



TO-18



TO-92

CASE	TYPE NO.	$r_{DS(on)}$ (Ohm)	V_{GS} (off) (V)		I_{DSS} (mA)		$V_{(BR)GSS}$ (V)	C_{iss} (pF)	C_{rss} (pF)	t_{on} (ns)	t_{off} (ns)	PIN OUT
		MAX	MIN	MAX	MIN	MAX	MIN	MAX	MAX	MAX	MAX	
TO-18	2N3970	30	4.0	10	50	150	40	25	6.0	20	30	SDG
TO-18	2N3971	60	2.0	5.0	25	75	40	25	6.0	30	60	SDG
TO-18	2N3972	100	0.5	3.0	5.0	30	40	25	6.0	80	100	SDG
TO-18	2N4091	30	5.0	10	30	--	40	16	5.0	25	40	SDG
TO-18	2N4092	50	2.0	7.0	15	--	40	16	5.0	35	60	SDG
TO-18	2N4093	80	1.0	5.0	8.0	--	40	16	5.0	60	80	SDG
TO-18	2N4391	30	4.0	10	50	150	40	14	3.5	15	20	SDG
TO-18	2N4392	60	2.0	5.0	25	75	40	14	3.5	15	35	SDG
TO-18	2N4393	100	0.5	3.0	5.0	30	40	14	3.5	15	50	SDG
TO-18	2N4856	25	4.0	10	50	--	40	18	8.0	9.0	25	SDG
TO-18	2N4856A	25	4.0	10	50	--	40	10	4.0	8.0	20	SDG
TO-18	2N4857	40	2.0	6.0	20	100	40	18	8.0	10	50	SDG
TO-18	2N4857A	40	2.0	6.0	20	100	40	10	3.5	10	40	SDG
TO-18	2N4858	60	0.8	4.0	8.0	80	40	18	8.0	20	100	SDG
TO-18	2N4858A	60	0.8	4.0	8.0	80	40	10	3.5	16	80	SDG
TO-18	2N4859	25	4.0	10	50	--	30	18	8.0	9.0	25	SDG
TO-18	2N4859A	25	4.0	10	50	--	30	10	4.0	8.0	20	SDG
TO-18	2N4860	40	2.0	6.0	20	100	30	18	8.0	10	50	SDG
TO-18	2N4860A	40	2.0	6.0	20	100	30	10	3.5	10	40	SDG
TO-18	2N4861	60	0.8	4.0	8.0	80	30	18	8.0	20	100	SDG
TO-18	2N4861A	60	0.8	4.0	8.0	80	30	10	3.5	16	80	SDG
TO-92	2N5555	150	--	--	15	--	25	5.0	1.2	10	25	DSG
TO-92	PN4091	30	5.0	10	30	--	40	16	5.0	25	40	DSG
TO-92	PN4092	50	2.0	7.0	15	--	40	16	5.0	35	60	DSG
TO-92	PN4093	80	1.0	5.0	8.0	--	40	16	5.0	60	80	DSG
TO-92	PN4391	30	4.0	10	50	150	40	14	3.5	15	20	DSG
TO-92	PN4392	60	2.0	5.0	25	75	40	14	3.5	15	35	DSG
TO-92	PN4393	100	0.5	3.0	5.0	30	40	14	3.5	15	55	DSG

P-Channel

TO-18	2N5114	75	5.0	10	30	90	30	25	7.0	16	21	SGD
TO-18	2N5115	100	3.0	6.0	15	60	30	25	7.0	30	38	SGD
TO-18	2N5116	150	1.0	4.0	5.0	25	30	25	7.0	50	80	SGD

*Some JFET types available on special order only; please consult factory

(25-June 2012)

Central[™]
Semiconductor Corp.
www.centalsemi.com

OUTSTANDING SUPPORT AND SUPERIOR SERVICES



PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- Consolidated shipping options
- Custom bar coding for shipments
- Custom product packing

DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2nd day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities
- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- Application and design sample kits
- Custom product and package development

CONTACT US

Corporate Headquarters & Customer Support Team

Central Semiconductor Corp.
145 Adams Avenue
Hauppauge, NY 11788 USA
Main Tel: (631) 435-1110
Main Fax: (631) 435-1824
Support Team Fax: (631) 435-3388
www.centalsemi.com

Worldwide Field Representatives:
www.centalsemi.com/wwreps

Worldwide Distributors:
www.centalsemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: www.centalsemi.com/terms