


连接器针位 vs 引线颜色



Technical drawing of a mechanical part. The drawing shows a 30-degree chamfer and a 0.7mm fillet. The drawing includes a section line and a key symbol.

Exciting Sequence vs. Direction of Rotation

STEP	A	B	C	D
1	+	+	-	-
2	-	+	+	-
3	-	-	+	+
4	+	-	-	+

CCW

10. 绝热等级 Insulation Cla

铭牌 Label Detail

齿型 Profile	MXL
齿数 Number of Teeth	20
节距 Pitch	2.032
节圆 Pitch Diameter	Ø12.94
齿顶圆 Outside Diameter	Ø12.43 ^{+0.05} ₀
材料 Material	HPb59-1

MOONS' STEPPING MOTOR
TYPE MS17HA4L4100-02
XXXXXXXX YY/MM/DD

Work Order 加工程号

未注公差 Tolerances for linear and angular dimensions without individual tolerance indications	GB/T 1804-m eqv ISO 2768-1□m
未注形位公差 Geometrical tolerance for features without individual tolerance indications	GB/T 1184-K eqv ISO 2768-2□K

设计 Design

Shanghai Moons' Electric Co., Ltd.

This document is released for information only. Its reproduction in whole or in part or its dissemination to third parties is prohibited. All trademarks and registered trademarks appearing on this document are the property of their respective owners.

Type: MS17HA4L4100-02 Rev.D SCALE 1:1 Sheet 1 of 1

8