

Part Number : [194130099](#)

Product Description : Solderless Terminals Kit,
Partial Insulated Quick Disconnects, 280 Pieces

Series Number : 19413

Status : Active

Product Category : Kits

Engineering Part Number : KIT-MX4



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771- DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Kits
Series	19413
Description	Solderless Terminals Kit, Partial Insulated Quick Disconnects, 280 Pieces
Comments	Includes (40) of part numbers 190170047 and 190230008, and (50) of part numbers 190170037, 190170014, 190230012, and 190230005. See Kit Components below for links to included parts.
Component Type	Kit
Kit Component Parts	<p>InsulKrimp Quick Disconnect, Female, for 10-12 (5.00-3.30mm²) Wire, Box, Tab 6.35 x 0.81mm, Carton, InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm²) Wire, Box, Tab 6.35 x 0.81mm, Carton, InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²) Wire, Box, Tab 6.35 x 0.81mm, Carton, InsulKrimp Fully Insulated Quick Disconnect, Male, for 12-10 AWG (5.00-3.30mm²) Wire, Tab 6.35 x 0.81mm, Carton, InsulKrimp Fully Insulated Quick Disconnect, Male, for 16-14 AWG (2.00-1.30mm²) Wire, Tab 6.35 x 0.81mm, Carton, InsulKrimp Fully Insulated Quick Disconnect, Male, for 22-18 AWG (0.80-0.35mm²) Wire, Tab 6.35 x 0.81mm, Carton</p>
Product Name	Solderless Terminals Kit
UPC	191128415064

Physical

Circuits (Loaded)	N/A
Depth	32.00mm
Length	210.00mm
Width	114.00mm

Kit Component Parts

Description	Part Number
InsulKrimp Quick Disconnect, Female, for 10-12 (5.00-3.30mm ²) Wire, Box, Tab 6.35 x 0.81mm, Carton	<u>190170047</u>
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm ²) Wire, Box, Tab 6.35 x 0.81mm, Carton	<u>190170037</u>
InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²) Wire, Box, Tab 6.35 x 0.81mm, Carton	<u>190170014</u>
InsulKrimp Fully Insulated Quick Disconnect, Male, for 12-10 AWG (5.00-3.30mm ²) Wire, Tab 6.35 x 0.81mm, Carton	<u>190230008</u>
InsulKrimp Fully Insulated Quick Disconnect, Male, for 16-14 AWG (2.00-1.30mm ²) Wire, Tab 6.35 x 0.81mm, Carton	<u>190230012</u>
InsulKrimp Fully Insulated Quick Disconnect, Male, for 22-18 AWG (0.80-0.35mm ²) Wire, Tab 6.35 x 0.81mm, Carton	<u>190230005</u>

This document was generated on May 27, 2026