

Search within category **GO**

**BUY NOW**

**DESIGN / INSTALL**



**CJSJ5E88TGY**

Category 5e, RJ45, 8-position, 8-wire shielded spring shuttered universal jack module.

<span>Specs</span> <span>Packaging Details</span> <span>Documents</span> <span>★ Add to Favorites</span> <span>🛒 Add to BOM</span>	
Performance Level	Category 5e
Color	Black
Termination Style	Giga-TX (TG Style)
Storage Temperature	-40°F to 158°F (-40°C to 70°C)
Application	Shielded
Depth (In.)	1.5
Depth (mm)	38.1
Height (In.)	0.75
Material	ABS/Tin Plated Over Phosphorous Bronze//Plastic
Module Type	Mini-Com
Operating Temperature	-14°F to 149°F (-10°C to 65°C)
Wiring Scheme	T568A/T568B
RoHS Compliancy Status	Compliant
Min. Order Qty.	1