

Part Number : 1300170009
Product Description : Mini-Change Field Attachable, Male Connector, 3 Pole, Cable Range: 5.08-11.43mm Outside Diameter with Internal Threads, Stainless Steel
Series Number : 130017
Status : Active
Product Category : Industrial Connectors
Engineering Part Number : 1A3002-348

Documents and Resources

Drawings

1300170009_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Industrial Connectors
Series	130017
Description	Mini-Change Field Attachable, Male Connector, 3 Pole, Cable Range: 5.08-11.43mm Outside Diameter with Internal Threads, Stainless Steel
IP Rating	IP67
Product Name	Mini-Change
Type	Field Attachable Connector
UPC	78678853653

Agency

CSA	LR6837

Electrical

Current - Maximum per Contact	13.0A
Voltage - Maximum	600V AC/DC

Physical

Cable Diameter	5.08-11.43mm (.200-.450")
Coupling Type	Internal Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	Single
Material - Connector Body	Nylon
Material - Contact	Copper Alloy
Material - Coupling Nut	Stainless Steel Type 316
Material - Plating Mating	Gold
Net Weight	45.359/g
Orientation	Straight
Poles	3

Downloaded from Arrow.com.

Temperature Range - Operating	-20° to +80°C
Wire Size (AWG)	15 to 24

Downloaded from Arrow.com.