



Part Number : 1301380076
Product Description : Watertite Multiple Outlet Pendant Box, (2) NEMA 5-20 Duplex with Flip Lids, 7.62m (25.0') Cord Length, 12/3 SOOW Cord, Double Eye Wire Mesh Support Grip
Series Number : 130138
Status : Active
Product Category : Power Distribution
Engineering Number : 70W33A123



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Relevant

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power Distribution
Series	130138
Description	Watertite Multiple Outlet Pendant Box, (2) NEMA 5-20 Duplex with Flip Lids, 7.62m (25.0') Cord Length, 12/3 SOOW Cord, Double Eye Wire Mesh Support Grip
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA 5-20
Product Name	Watertite
Type	Multiple Outlet Box
UPC	78678801664

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
GFCI Reset	N/A
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	N/A

Physical

Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	7.62m (25.0')
Cord Type	12/3 SOOW
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber
Mounting Style	Portable
Net Weight	421.000/g
Number of Receptacles	2
Packaging Type	Carton
Receptacle Type	Duplex

This document was generated on Apr 26, 2025