

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0050291900
Status: Active
Overview: KK® Interconnect System - Molex
Description: KK® High Pressure Crimp Terminal 7879, 24-30 AWG, Reel Tin (Sn)

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Crimp Terminals
Series	7879
Application	Signal
Crimp Quality Equipment	Yes
Overview	KK® Interconnect System - Molex
Packaging Alternative	46999-0101 (Loose)
Product Name	KK® High Pressure
UPC	822348742165
Physical	
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Nickel
Net Weight	0.118/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.57mm max.
Wire Size AWG	24, 26, 28, 30
Wire Size mm²	N/A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	7879-1(P154)
Reference - Drawing Numbers	
Sales Drawing	SD-7879



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC Not Contained Per - ED/30/2017 (7 July 2017) Halogen-Free Status Low-Halogen Need more information on product environmental compliance? Email productcompliance@molex.com Please visit the Contact Us section for any non-product compliance questions.	China RoHS China ROHS ELV RoHS Phthalates
	Green Image Not Relevant Not Contained

Search Parts in this Series
[7879 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION