

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	ECR-20-004655	06OCT20	RK	SBH

NOTE:


1. PACKAGING ACC. TO TE SPEC.107-18032
BUNDLE EVERY 25 ASSEMBLIES WITH A RUBBER BAND
2. ELECTRICAL TEST CONTAINING "SHORT CIRCUIT TEST, CONTINUITY
AND ACCURATE CAVITY ASSIGNMENT TEST" ACC. TO
TE-SPEC.108-18857, SUBSECTION 3.1.1
3. ASSEMBLY COLOR: WHITE

4 KEYING ACC. TO TABLE


4

PN	KEYING
1--X	HV-3
2--X	LV-2

OBSOLETE	PN	L	TOLERANCES/mm
	X-2083077-1	610mm (2ft)	+/- 5
	X-2083077-2	1270mm (4ft)	+/- 15
	X-2083077-3	1880mm (6ft)	+/- 20
	X-2083077-4	2490mm (8ft)	+/- 20
	X-2083077-5	3100mm (10ft)	+/- 30
	X-2083077-6	3660mm (12ft)	+/- 30
	X-2083077-7	4270mm (14ft)	+/- 50
	X-2083077-8	4880mm (16ft)	+/- 50



mm	AR	AR	Cable SVT 2xAWG18 UL WH	4
PC	2	2	MICRO QUADLOK SYSTEM PIN CONTACT	3
PC	1	1	TUBE FOR SVT CABLE	2
PC	-	1	OUTLET, MINI HVL 7.5mm HV-3	1
PC	1	-	OUTLET, MINI HVL 7.5mm LV-2	
UOM	QTY	QTY	DESCRIPTION	POS.
	2--X	1--X		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SATHISH KUMAR.G CHK R.HOSSAINI APVD R.HOSSAINI PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		08APR11 08APR11 08APR11		 TE Connectivity					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		NAME CABLE ASSEMBLY NECTOR S LINE 2POS. HV-3 AND LV-2 —							
											
MATERIAL —		FINISH —		SIZE A3		CAGE CODE 00779		DRAWING NO C-2083077		RESTRICTED TO —	
CUSTOMER DRAWING						SCALE NTS		SHEET 1 OF 1		REV D1	