



Pushing Performance
Since 1945

FO CA SCdx-SCdx 2G50/125 OM3, 10.0m




Image is for illustration purposes only. Please refer to product description.

Part number	33 01 241 0100 006
Specification	FO CA SCdx-SCdx 2G50/125 OM3, 10.0m
HARTING eCatalogue	https://harting.com/33012410100006

Identification

Category	System cabling
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	SC duplex
Connector 2	SC duplex
Type of cable	FO cable
Description of the cable	Multimode

Version

Cable length	10 m
Number of fibres	2
Fiber type	2G50/125 OM3

Technical characteristics

Cable diameter	5.17 mm
----------------	---------

Material properties

Colour (cable)	Light blue
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol
ECHA SCIP number	8a5c37c3-d5dc-469f-b994-a066c654819f
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Net weight	186 g
Country of origin	Latvia
European customs tariff number	85447000
GTIN	5713140249349
eCl@ss	27061003 Patch cable fiber-optic